



## Grinding wheel E 125x7.2x22.23 mm CERAMIC Performance Line SG STEELOX for steel/stainless steel

**Grinding wheel E 125x7.2x22.23 mm CERAMIC Performance Line SG STEELOX for steel/stainless steel**

Item number: [62212300](#)

EAN: [4007220007129](#)

Special Line SGP tools are specially developed for specific tasks and offer the user key advantages over conventional products. Furthermore, the Special Line SGP includes tools that offer ultimate economic efficiency thanks to their particularly high performance during use.

High-performance grinding wheel with ceramic oxide grain for quick and economical grinding.

### Technical information

Abrasive	Ceramic oxide grain
Dia. external	125 mm
Dia. hole	22.23 mm
Max. RPM	12200 RPM
Shape	E / 27 / T27
Width	7.2 mm

## Advantages

- ✔ The ultimate in aggressive performance and excellent tool life due to the self-sharpening effect of the ceramic oxide grain high-performance abrasive in connection with a special bond technology.
- ✔ Labour cost savings due to much faster work progress compared to conventional grinding wheels.
- ✔ Labour-saving work.

---

## Materials that can be worked

- ✔ Stainless steel (INOX)
- ✔ Steel

---

## Applications

- ✔ Chamfering
- ✔ Deburring
- ✔ Grouting
- ✔ Surface grinding
- ✔ Work on fillet welds
- ✔ Work on weld seams

---

## Drive types

- ✔ Angle grinder
  - ✔ Drive spindle
- 

**PFERD  
TOOLS**



August Rüggeberg GmbH & Co. KG  
Hauptstraße 13  
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

[info@pferd.com](mailto:info@pferd.com)