

ave as PDF



HeadsUp Lite™ 2690 LED Flashlight



Regardless of the season, Peli\'s new 2690 HeadsUp Lite™ won\'t leave you in the dark. With 60 lumens of LED light, 10 hours of battery burn time and weighing in at 4.1 ounces (117 grams), it\'s brighter, more efficient, compact and lighter than other headlamps in its class. The no-nonsense rotary bezel switch is easy to operate, even when wearing bulky gloves. The 2690 is made of impact and chemical resistant ABS and it\'s water resistant for all-weather use. It comes with an adjustable and comfortable cloth strap, as well as a heavy duty rubber strap that will not slip off your climbing helmet. Peli\'s new 2690 HeadsUp Lite™ is engineered for those who take the outdoors seriously. Use your head. Get the 2690 HeadsUp Lite™ from Peli.



HeadsUp Lite™ 2690 LED Flashlight ANSI FL1 Specifications

Hiah					
LIGHT SOURCE.	LED				
BATTERIES	3 AAA Alkaline (Included)				
CHARGE TIME					
VOLTAGE	4.5				
LENGTH	7.1 cm (2.81")				
WEIGHT W/ BATTERIES	0.13 kg (4.5 oz.)				
WEIGHT W/O BATTERIES	0.08 kg (2.8 oz.)				


LIGHT OUTPUT

RUNTIME (hours/min)

BEA M DISTA NCE

(meters)

PEAK BEAM
INTENSITY
(candela)



Materials

Body	Lens	Shroud	Switch Type	
ABS	PC	ABS	One hand rotary switch operation	
Clip	Contact, Spring & Retainer		O- Ring	Night Vision Film
N/A	Phosphore Bronze Nickel Plate		EPDM	N/A

Configuration

HeadsUp Lite™ 2690 LED Flashlight Accessories

No accessories are currently available for this product

Approvals

CE S - I M1 Ex ia I Ma, II 1 G Ex ia IIC T4 Ga, Ex ia IIIC T65°C Da IP65
Certificate: TRL 08ATEX11184X

IECEX - IECEX TRC 11.0010X Ex ia I Ma, Ex ia IIC T4 Ga, Ex ia IIIC T65°C

- Class I II III Div. 1 GRPS ABCDEFG T4
- Class I II III Div. 1 GRPS ABCDEFG T4