



# PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 8:01 (UTC)



## 22315EAKE4

### Spherical Roller Bearings

#### Parts Number

22315EAKE4C3
--------------

#### Boundary Dimensions

d	75	mm	Bore diameter
D	160	mm	Outside diameter
B	55	mm	Width
r (min.)	2.1	mm	Chamfer dimension

#### Basic Load Ratings

Cr	485000	N	Basic dynamic load rating
C0r	505000	N	Basic static load rating

#### Speeds

Thermal Speed Rating (Oil-bath)	3400	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	4300	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	2800	min-1	Grease lubrication
Oil (Oil-bath)	3600	min-1	Oil-bath lubrication

#### Abutment and Fillet Dimensions


da (min.)	87	mm	Diameter of shaft abutment
da (max.)	97	mm	Diameter of shaft abutment
Da (min.)	137	mm	Diameter of housing abutment
Da (max.)	148	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

#### Calculation factors

e	0.33	Constant
Y2	3	Axial load Factors
Y3	2	Axial load Factors
Y0	2	Axial load Factors

#### Mass

Mass approx.	5.26	kg	Mass approx.
--------------	------	----	--------------



#### Associated products

Adapter	H2315X	Adapter
Withdrawal sleeve	AHX2315	Withdrawal sleeve