

RS Part Number: **9143998**

Europa Part Number: **RG25-1022-28-1024**

Specifications and dimensions



- 2PNO Power Relay
- Din Rail Mounting

Features	
Height	72mm
Width	26mm
Depth	49mm
Weight	0.13Kg
Cover ingress protection	IP20
Contact arrangement	2P NO
Contact material	AgCdO
Rated switching voltage	400V AC
Minimum switching voltage	10V
Rated load AC1	25A / 400VAC
Rated load AC3	15A / 400VAC
Rated load DC1	25A / 24V
Rated voltage coil	24V DC
Rated power consumption of coil	1.7W
Dielectric strength coil-contacts	5000 VAC
Operating time	20ms
Release time	20ms
Electrical life AC1	> 10 ⁵
Mechanical life	> 10 ⁶
Operating temperature	,-25°C to +85°C
Related Products	
ABS Enclosure IP67 for relays 110mm cubed	PB6110D

① ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Information provided in data sheets and/or specifications may vary from actual results in different applications and performance may vary over time. **All products must be installed according to manufacturers instructions.**

Europa House, Airport Way, Luton, Beds, LU2 9NH Tel: 01582 692 440 / Fax: 01582 692 450 e-mail: sales@europacomponents.com
website: <http://www.europacomponents.com>