



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	C220466	2022/04/13	Ruru	 X5
D	C230086	2023/01/31	Ruru	 X1
E	C241346	2025/01/20	Victor Hung	 X3






Recommended
Panel Cut-out




BB-XXRMMS-QC800I

XX: No. Of Pin—



Note: 

- * RoHS Compliant
 - *  Important dimension
 - *  Waterproof rate: IP68, unmated 1m/24h
 - * Connector
- Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
- * Nut: Thermoplastic, Black
 - * Gasket: Rubber, Gray
 - * For panel thickness max: 4.5mm
 - * Gasket and nut are packed separately in pe bag



Pin Assignment Front View

UNIT:mm				TITLE		XLOK, B-10A, REAR FASTENED	
TOLERANCE				M, M, SOLDER, PUSH LOCK			
.X ± 0.25 mm		SCALE 2:1		SIZE A4		SHEET 1 OF 1	
		REV. E		WC-REV. .0		QC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Victor Hung	DATE 2025/01/20
DWG NO BB-XXRMS-QC8001 	CHECKED BY Neo Tasi	DATE 2025/01/20
CUSTOMER ALTW	APPROVED BY Fred Lee	DATE 2025/01/20