

TSI Code: 398252654

Price\*: 295.00 GBP



## Main

Range	Spacial
Product name	Spacial S3X
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	400 Mm
Enclosure nominal width	600 Mm
Enclosure nominal depth	200 Mm
Installation accessory type	Wall-mounting
Device composition	1 body 1 lock: door 1 door

## Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Plain
Number of doors	Front face: 1 door(s)
Door opening side	Reversible (120 °)
Lock type	3 mm double-bar lock
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door: stainless steel 304L Lock: zamak Hinge: stainless steel
Surface finish	Body and door: Scotch-Brite® brushed Lock: chromium plated
Net weight	9.124 Kg

## Environment

Standards	IEC 62208
Product certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Environmental characteristic	Specific hygiene Corrosive

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	9.124 Kg
Package 1 Height	62 Cm
Package 1 width	41 Cm
Package 1 Length	22 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**