

Features

- Very small size miniature camera
- 5Mp Image Sensor
- Compress Format :H264/MJPEG
- Support Onvif
- POE Cable
- Corridor Mode
- HTML5 H.264 Streaming Support
- 2.1mm wide angle Lens

RS PRO CCTV Cameras

RS Stock No.: 0291734



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *This Miniature CCTV Camera is used for surveillance and security purposes*
- *It shoots and transmits video to NVR or VSM used with camera.*

General Specifications

Indoor/Outdoor	Indoor
Analogue/Network	Network
For Outdoor Use	No
Form Factor	Fixed Miniature
Sensor Size	5MP (Megapixels)
Vandal Resistant	No
IR	No
Audio Support	No
360/180 Panoramic View	No
Wireless	No
ONVIF	Yes
Ruggedized - (EN50155)	No
Colour	white
On-board storage	No
Camera Connection Type	RJ45
Mounting method	wall
Housing	Aluminium

Camera Specifications

Sensor Type	1/2.7 Omnivision PureCel® CMOS
Resolution	2592x1944 / 2560x1440 / 2048x1536 / 2304x1296 / 1920x1080 / 1280x720
Maximum Resolution	2592x1944 pixels
Scanning System	Progressive
Electronic Shutter	NTSC : 1/30 -1/30.000 sec (Auto) PAL: 1/25-1/30,000 sec (Auto)
Lens	Mega f= 2.1mm Wide Angle
Horizontal Field of View	5M [4:3] H131.20° × V:99.53° / 4M [16:9] H:131.20° × V:72.05°
Video Output	IP
Max. video recording quality	1944P
S/N	More than 52 dB(AGC Off)
Storage memory	No
Video Frame Rate	30fps@all resolution
Gamma Correction	YES

OSD Functions

White Balance	Auto / Manual
Exposure	MANUAL
Shutter Speed	AUTO / Manual (1/30 ~1/30.000)
SENS-UP	OFF, x2, x4
Backlight Compensation	BLC / D-WDR
Privacy Masking	4zone , Off / On
Day & Night	AUTO / Day / Night / CDS / Schedule
Corridor Mode	90° / 270°
3DNR	AUTO
Motion Detection	OFF / ON
Digital Effect	OFF/MIRROR V-FLIP/ROTATE
Sharpness / DEFOG	Adjustable / ON / OFF
Image Enhancement	D-WDR
Language	ENG / KOR / JAP / GER

Electrical Specifications

Dual Voltage	No
PoE - Power Over Ethernet	Yes
Power consumption	120 mA
Power Input	IEEE 802.3af , DC+12 V
Min. Illumination	COLOUR: 0.15 Lux

Mechanical Specifications

Dimensions	33.5x33mm
Focal Length	2.1.mm
Height	33.5mm
Width	33mm
Weight	Approx. 100 g included bracket

Operation Environment Specifications

Operating Temperature	-20° C to +50° C
Storage Temperature	-30° C to +60° C
Humidity	90%