

**Metal drill bits HSS PointTeQ**

PRODUCT PROPERTIES					ORDERING INFORMATION				Part number
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Diameter (D) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	
-	52	80	-	5/32	P1h	10	1	3165140908313	2 608 577 322
-	55	84	-	11/64	P1h	10	1	3165140908320	2 608 577 323
-	60.5	90	-	3/16	P1h	10	1	3165140908337	2 608 577 324
-	63.5	93	-	13/64	P1h	10	1	3165140908344	2 608 577 325
-	65.5	96	-	7/32	P1h	10	1	3165140908351	2 608 577 326
-	68.5	99	-	15/64	P1h	10	1	3165140908368	2 608 577 327
-	72	104	-	1/4	P1h	10	1	3165140908375	2 608 577 328
-	75	107	-	17/64	P1h	10	1	3165140908382	2 608 577 329
-	77	110	-	9/32	P1h	10	1	3165140908399	2 608 577 330
-	80	113	-	19/64	P1h	10	1	3165140908405	2 608 577 331
-	83	116	-	5/16	P1h	10	1	3165140908412	2 608 577 332
-	86.5	119	-	21/64	P1h	10	1	3165140908429	2 608 577 333
-	89.5	123	-	11/32	P1h	10	1	3165140908436	2 608 577 334
-	91.5	126	-	23/64	P1h	10	1	3165140908443	2 608 577 335
-	95	130	-	3/8	P1h	10	1	3165140908450	2 608 577 336
-	98	133	-	25/64	P1h	10	1	3165140908467	2 608 577 337

Pack of 5

10.2	87	133	10.2	-	P1h	5	1	3165140907798	2 608 577 270
10.5	87	133	10.5	-	P1h	5	1	3165140907828	2 608 577 273
10.6	87	133	10.6	-	P1h	5	1	3165140907835	2 608 577 274
10.7	94	142	10.7	-	P1h	5	1	3165140907842	2 608 577 275
10.8	94	142	10.8	-	P1h	5	1	3165140907859	2 608 577 276
10.9	94	142	10.9	-	P1h	5	1	3165140907866	2 608 577 277
11	94	142	11	-	P1h	5	1	3165140907873	2 608 577 278
11.1	94	142	11.1	-	P1h	5	1	3165140907880	2 608 577 279
11.2	94	142	11.2	-	P1h	5	1	3165140907897	2 608 577 280
11.3	94	142	11.3	-	P1h	5	1	3165140907903	2 608 577 281
11.4	94	142	11.4	-	P1h	5	1	3165140907910	2 608 577 282
11.5	94	142	11.5	-	P1h	5	1	3165140907927	2 608 577 283
11.6	94	142	11.6	-	P1h	5	1	3165140907934	2 608 577 284
11.8	94	142	11.8	-	P1h	5	1	3165140907958	2 608 577 286
11.9	101	151	11.9	-	P1h	5	1	3165140907965	2 608 577 287
12	101	151	12	-	P1h	5	1	3165140907972	2 608 577 288
12.1	101	151	12.1	-	P1h	5	1	3165140907989	2 608 577 289
12.2	101	151	12.2	-	P1h	5	1	3165140907996	2 608 577 290
12.3	101	151	12.3	-	P1h	5	1	3165140908009	2 608 577 291
12.4	101	151	12.4	-	P1h	5	1	3165140908016	2 608 577 292
12.5	101	151	12.5	-	P1h	5	1	3165140908023	2 608 577 293
12.6	101	151	12.6	-	P1h	5	1	3165140908030	2 608 577 294
12.7	101	151	12.7	-	P1h	5	1	3165140908047	2 608 577 295
12.8	101	151	12.8	-	P1h	5	1	3165140908054	2 608 577 296
13	101	151	13	-	P1h	5	1	3165140908078	2 608 577 298
-	101	136	-	13/32	P1h	5	1	3165140908474	2 608 577 338
-	103	140	-	27/64	P1h	5	1	3165140908481	2 608 577 339
-	106	143	-	7/16	P1h	5	1	3165140908498	2 608 577 340
-	109	146	-	29/64	P1h	5	1	3165140908504	2 608 577 341
-	113	149	-	15/32	P1h	5	1	3165140908511	2 608 577 342
-	114	152	-	31/64	P1h	5	1	3165140908528	2 608 577 343
-	118	156	-	1/2	P1h	5	1	3165140908535	2 608 577 344