
RS PRO Flat Padlock Eye - Medium - Set of 10

RS Stock No.: 0802220



Features

- Surface-mounted stainless steel padlock eye
- Designed for LOTO retrofitting
- Supports single or multiple padlocks
- Compatible with lockout hasps
- Corrosion-resistant solid steel
- Universal padlock compatibility
- Screw, bolt, or rivet installation
- Suitable for electrical panels & machinery
- Enhances OSHA compliance

RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Ideal for Retrofitting Existing Equipment*** *- Adds lockout/tagout capability to machinery, panels, and equipment lacking integrated isolation points.*
- ***Supports LOTO Compliance*** *- Designed to help organisations meet OSHA lockout/tagout safety requirements.*
- ***Secure Padlock Attachment Point*** *- Provides a strong and reliable fixing point for one or multiple padlocks.*
- ***Compatible with Lockout Hasps*** *- Allows group lockout procedures by accommodating multiple padlocks via a hasp.*
- ***Ensures Positive Isolation*** *- Keeps machinery secured in the "off" position until every applied padlock is removed.*
- ***Surface-Mounted Design*** *- Easily installed on electrical panels or areas where traditional isolation points may be inaccessible.*
- ***Solid Stainless-Steel Construction*** *- Manufactured from consistent-thickness stainless steel for durability and corrosion resistance.*

General Specifications

Type	Padlock Accessories
Material	Stainless steel
Colour	Metallic Silver
Padlock holes	01
Package	PE-LD

Mechanical Specifications

Dimensions	48mm X 25mm
Height	48mm
Width	25mm
Hole Diameter	9.5mm
Weight	80 Grams

Operation Environment Specifications

Withstand temperature	-40°C to 120°C

