



Combinations for connectors in Gel filled boxes

Series	Color	Material	Temperature	Dimensions	Weight	Part No.
SC-5	Green	PP	-40-105 °C	18 x 21.6 x 29.7 mm	0.15 g	0240-PP8

SC-5 0240-PP8

E1441298

Splicing Connector, 5-Conductors, 0.2-4.0mm², AWG 28-12, with Lever



Product Properties:

Number of clamp positions (device side)	5 .
Type of locking/unlocking	Lever
Nominal voltage	450 V
Nominal current	32 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	5 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	12 mm
Colour	Green
Operating temperature	-40-105 °C
Connector type	Topplämma, öppningsbar
Flammability rating (UL94)	V2

Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.2-4 mm ²
Nominal cross section (installation side)	0.2-4 mm ²

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm ²
Conductor cross section solid (solid, stranded)	0.5-4 mm ²
Width	90 mm
Height	11 mm
Strip length	12 mm
MOQ	10 .
Unit	pck
Nominal cross section	0.2-4 mm ²
Length	30 mm
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Contain no Iron or Steel
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Consumer pack
Search Description	SKH2023ERIK1 ENR2023V ANSLUTNINGSKLÄMMA, EFO2025H
Alternative SKU	SC-50240-PP8
E-no	E1441298

Logistic information:

Barcode	733117641176
Country of origin	CN
E-no	E1441298
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	SC-5 0240-PP8

Taric code

85369010

Unit

pck

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se