

NRL RABS/Isolator gloves with heavyweight thickness, for better abrasion and tear resistance

Port size: 152mm/6"

Thickness: 0.76mm/30 mil

- **Sustained protection:** AlphaTec® NRL RABS and Isolator Gloves 55-101 boast EN388:2016 Level 2 tear and abrasion resistance capabilities
- **Improved durability:** Heavyweight thickness grants these RABS gloves even greater durability, for longer wear life
- **Limited contamination risks:** These NRL gloves' translucent, unlined nature reduces the risk of potential contamination and facilitates the cleaning process

KEY FEATURES & BENEFITS

- **EN 388:2016 compliance:** For superior abrasion and tear resistance
- **Heavyweight thickness:** Greater durability, longer-lasting glove life
- **Unlined:** Reduced contamination risks and easy to clean



TECHNICAL DATA SHEET

Product Reference	55-101
Material	Natural Rubber Latex
Color	Natural
Shape	Ambidextrous
External Glove Surface	Smooth
Cuff Style	Beaded
Storage Instructions	Store in a dry and dark environment, temperature of 5°C to 22°C. Retain in original packaging when not in use.
Available Sizes	8, 9, 10
Temperature Range	From -30°C to 50°C
Shelf Life	Three (3) years from date of manufacture.
Standards	CE 0493, EN 388:2016, EN ISO 21420:2020, EN ISO 374-1:2016 Type A (KLMNPT), EN ISO 374-5:2016, Category III, UKCA
Vulcanization Chemical Accelerators	• Natural rubber proteins • Zinc Diethyldithiocarbamate (ZDEC)

PHYSICAL PROPERTIES

	Typical Values	Testing Method
Typical Length (mm/in)	711 / 28	EN 455-2
Port Size	152mm/6"	
Target Single Wall Palm Thickness (mm/mil)	0.76 / 30	EN 455-2
Target Single Wall Cuff Thickness (mm/mil)	0.76 / 30	EN 455-2

PROTECTION AGAINST MECHANICAL RISKS, EN 388:2016+A1:2018

Risk	Performance level
Abrasion Resistance	Level 2
Blade Cut Resistance	Level 1
Tear Resistance	Level 2
Puncture Resistance	Level 1
ISO 13997 Cut Resistance	Level A

ORDERING INFORMATION

	PORT SIZE	6"/152mm	6"/152mm	6"/152mm
	SIZE	8	9	10
55-101	REORDER NO.	55101080	55101090	55101100

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
US T: +1 800 800 0444
US F: +1 800 800 0445
CA T: +1-800-363-8340

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
T: +61 1800 337 041
F: +61 1800 803 578

UK

Ansell Nitritex
T: +44 1638 663338
F: +44 1638 668890

Performance Standards and Regulatory Compliance



Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.