



AS SC-2345S246 TL10



AS SC-2345S246 TL10

Assortment box of 105pcs, Releasable Splicing connectors

Product Properties:

Nominal voltage	450 V
Nominal current	32 A
Transparent	Yes
Number of clamp positions	2-6 .
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Green

Dimensions:

Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-4 mm²
Conductor cross section solid (solid, stranded)	0.2-4 mm²
MOQ	1 .

Unit	pcs
Nominal cross section	0.2-4 mm²
Nominal voltage	450 V

Approvals:

Compliance:

REACH	No SVHC (Latest. 21 Jan 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	SKV2024ERIK3
Alternative SKU	ASSC-2345S246TL10

Logistic information:

Barcode	733117614963
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS SC-2345S246 TL10
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.