



# 8910DPA32V14

## CONTACTOR 600VAC 30AMP DPA +OPTIONS


[Download your 8910DPA32V14 datasheet](#)

[Characteristics](#) | [Documents & Downloads](#)

### Main Hide

Product or component type	Definite Purpose Contactor
[In] rated current	30 A
Motor power hp	2 hp 115 V AC 1 phase 5 hp 230 V AC 1 phase
Poles description	2P
Pole contact composition	2 NO
Control circuit voltage	24 V AC 50/60 Hz

### Complementary Hide

Product certifications	CE CSA UL listed
Locked rotor rated current	150 A 460 V AC 120 A 575 V AC 180 A 277 V AC
[Ue] rated operational voltage	600 V AC
Network number of phases	1 phase
Electrical connection	Quick connect terminals
Range of product	DPA

### Offer Sustainability Hide

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty Hide

Period	18 months
--------	-----------