



Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Anwendung	Multi-purpose
Nennmaße des Gehäuses	-
Mounting location	Step slide Back inserts
Mounting plate description	Plain
Range compatibility	Thalassa PLA Thalassa PHD
Device composition	1 mounting plate
Material	Galvanised steel

Complementary

Fixing mode	By screws - screw type M8 - on back inserts location
Permanent permissible load	150 kg
Height	1500 Mm nominal: 1390 mm real:
Width	750 Mm nominal: 625 mm real:
Depth	125 mm real:
Thickness	25 mm

Packing Units

Package 1 Weight	17.33 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.