

silencer


U-3/4

Part number: 2311

★ Core product range

FESTO

For reducing noise and avoiding contamination at the exhaust ports of pneumatic components.



Data sheet

Feature	Value
Assembly position	Any
Operating pressure	0 ... 10 bar
Flow rate to atmosphere	17,600 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Sound pressure level	85 dB(A)
Ambient temperature	-10 ... 70 °C
Product weight	83 g
Pneumatic connection	G3/4
Material of silencer insert	PE
Materials note	Free of copper and PTFE Conforms to RoHS