



# AH

## LEVER OPERATING



[Download your AH datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

### Main Hide

<b>Range of product</b>	L100/300
<b>Series name</b>	Severe duty
<b>Product or component type</b>	Limit switch lever
<b>Device short name</b>	L100/300
<b>Associated complete product</b>	HL100 HL300 HML100 HML300 L100 L300 ML100 ML300
<b>Movement of operating head</b>	Rotary
<b>Type of operator</b>	Aluminium spring return roller lever length: 2 in - offset: - -
<b>Type of roller</b>	1 steel center roller diameter: 0.75 in - width: 0.25 in
<b>Type of approach</b>	Lateral approach
<b>Positive opening</b>	Without

### Complementary Hide

<b>Switch actuation</b>	By 30° cam
<b>Product weight</b>	0.1 lb(US)

### Environment Hide

<b>Ambient air temperature for operation</b>	-10...185 °F
<b>Ambient air temperature for storage</b>	-10...185 °F
<b>Environmental characteristic</b>	Standard environment

### Offer Sustainability Hide

<b>Sustainable offer status</b>	Not Green Premium product
<b>RoHS (date code: YYWW)</b>	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty Hide

Period

18 months