

## 221 - Split dies




### **Standards:**

**NF ISO 261, ISO 261, DIN ISO 261**

### **Description:**

- ISO metric RH thread.
- Chrome-vanadium HSS hardened to 62/64 HRc (234 daN/mm<sup>2</sup>).
- Tapered adjusting screw.

	Diameter [mm]	Diameter D1 [mm]	Diameter D2 [mm]	Thickness E [mm]	Thickness E1 [mm]	Weight [g]
<b>221.10X150</b>	38.1	10.0	1.5	13.0	6.0	80.0
<b>221.12X175</b>	38.1	12.0	1.75	13.0	6.0	90.0
<b>221.14X200</b>	38.1	14.0	2.0	13.0	6.0	80.0
<b>221.16X200</b>	38.1	16.0	2.0	13.0	6.0	75.0
<b>221.18X250</b>	38.1	18.0	2.5	15.0	8.0	75.0
<b>221.3X50</b>	25.4	3.0	0.5	8.0	3.5	25.0
<b>221.4X70</b>	25.4	4.0	0.7	8.0	3.5	25.0
<b>221.5X80</b>	25.4	5.0	0.8	8.0	3.5	30.0
<b>221.6X100</b>	25.4	6.0	1.0	9.0	3.5	30.0
<b>221.7X100</b>	25.4	7.0	1.0	9.0	3.5	30.0
<b>221.8X125</b>	25.4	8.0	1.25	9.0	3.5	30.0
<b>221.9X125</b>	25.4	9.0	1.25	9.0	3.5	30.0