

Soft Polyurethane, Metric Size - TUS

TUS1208B-20

Datasheet

General series information

- Applicable tubing O.D.: Ø 4 to Ø 16 mm
- Operating temperature: -20 to 60 °C for air and 0 to 40 °C for water
- 29 colour variations.

Standard specifications

Size	1208 (O.D. Ø12, I.D. Ø8)
Color	B (Black)
Roll Length	20 m Roll
Pressure medium	Air
Maximum temperature of pressure medium	20 °C
Maximum operating pressure	0.6 MPa
Maximum ambient temperature	60 °C
Minimum ambient temperature	-20 °C (with no freezing)
Usable tubing material	Polyurethane
Weight	1.400 Kg

Additional information

Catalogue

[T_EU.pdf](#)