

Clamp meter up to 1,000 V AC, CAT IV incl. 2x AAA batteries (45219)



Wiha Werkzeuge GmbH
Obertalstraße 3-7 78136
Schonach
E-Mail: info.de@wiha.com
Tel.: +49 (0)7722 959-0



Order no.: 45219

Article number: SB25551

EAN: 4010995452193

Customs tariff number: 90303200

Simplifies your work: Large LCD display with background illumination for easy to read measurement results.

Increases your safety: Measure live electrical wires without open contacts.

Makes handling easier: Easy one-hand testing without electrical circuit interruption.

Increases your efficiency: All measurement functions relevant for electricians in a single measuring device.

Simplifies your work: An integrated flashlight function ensures optimal illumination.

Increases your process reliability: Precise measurement results thanks to LPF and TRUE-RMS measurement.

Application: For multi-functional use in different application locations.

Measuring category: CAT IV up to 1,000 V.

When working, for example, on electrical systems that cannot be switched off, current measurement is a major challenge. With the measuring caliper from Wiha, the caliper bracket can be used to carry out measurements without interrupting the electrical circuit. Handling is greatly facilitated by the remote single-hand testing. The test tips allow additional tests, voltage measurement in the AC and DC range, as well as resistance, frequency, and capacity measurements. They also allow continuity and diode tests. This multi-functionality significantly increases the efficiency. A large LCD display with background illumination and data hold function makes the measurement results immediately readable even beyond the measurement process. An additional signal sound indicates the current flow during the continuity check. In addition, the measuring caliper from Wiha has an integrated flashlight function, providing optimal illumination conditions even in poorly lit work environments. The LPF function, coupled with the True-RMS function increase the process safety of your test by providing interference-free effective values. According to the measurement category CAT IV up to 1,000 V the measuring caliper offers maximum safety for working directly on the sources of low-voltage installations. Protection rating IP40.

Customs tariff number

90303200

Blister pack	No
Overall length (mm)	220 mm
Country of origin (ISO 3166-1 Alpha 3)	CHN
Weight PU in grams	471