

2150 6,5

3C-Screwdriver

for slotted head screws

| | |
|-----------------------|-------------|
| Code | ETIM |
| 6679510 | EC000158 |
| EAN | UNSPSC |
| 4010886806746 | 27-11-17-01 |
| Country of origin | eCl@ss |
| Slovenia | 21-04-04-01 |
| Customs tariff number | |
| 82054000 | |



Article description

- Acc. to DIN ISO 2380-2, cutting edge according to DIN ISO 2380-1 Form A
- 3-component handles Power-Grip³ with hanging hole
- Ergonomic handle shape for accurate, non-tiring work
- Positive connection of handle and blade for optimum power transmission
- Type of drive marked at the end of the handle
- Blade of galvanised molybdenum-vanadium steel

Article information

| | | | |
|--------------------------|---------------------------|-------------------------------|-------------------------|
| Contents (Qty of pieces) | 1 | Cap rotatable | no |
| Version/Execution | with hanging hole | Anti-magnetic | no |
| Net weight [kg] | 0,128 kg | Ball head | no |
| Total length [mm] | 260 mm | Handle available | yes |
| Material | Molybdenum-vanadium-steel | Isolated | no |
| Blade length | 150 mm | Corrosion Protected | no |
| Standard | DIN ISO 2380-2 | Colour coding | no |
| Blade width [mm] | 6,5 mm | Unit-tested | no |
| Low sparking design | no | Handle design | 3C |
| Blade shape | Round | Output tip reference standard | DIN ISO 2380-1 - Form A |
| Blade diameter | 6,0 mm | Drive hexagon | no |
| Roll protection | no | Blade thickness | 1,2 mm |
| Impact cap | no | | |