



PG-19-F

**40 mm Expert Bypass Telescopic
Loppers with 2-Component Handle
700 mm - 900 mm**









PRODUCT DETAILS

- Blade with slicing cut is made of high-grade steel, fully-hardened
- Telescopic lopper with handles made of silver aluminium tubes, extendable from 70 cm to 90 cm
- Comfortable two-component grips made of orange polypropylene and soft black thermoplastic elastomer
- Shock absorbing rubber buffer
- Special locking system locks/unlocks with just a quarter-turn
- No spare parts available
- For pruning high trees with thick branches
- Lightweight aluminium handle
- Comfortable two-component handles giving an excellent grip
- Easy reach with the lightweight telescopic handles 70 cm to 90 cm
- Easy one-direction twist locking system



PRODUCT ATTRIBUTES

Product						
PG-19-F	40 mm	1 1/2 in	745 mm	29.33 in	1135 g	40,04 oz

Follow the Fish!

