



# OUR OFFER

## SIEMENS – SINAMICS V20

### SINAMICS V20 - The versatile inverter for basic solutions

#### Inverter Drives without Filter - 1-Phase - 200-240V

Stock-No.	Siemens MPN	Power Rate
784-0713	6SL3210-5BB11-2UV0	0.12 kW
784-0717	6SL3210-5BB12-5UV0	0.25 kW
784-0726	6SL3210-5BB13-7UV0	0.37 kW
784-0729	6SL3210-5BB15-5UV0	0.55 kW
784-0723	6SL3210-5BB17-5UV0	0.75 kW
784-0732	6SL3210-5BB21-1UV0	1.1 kW
784-0735	6SL3210-5BB21-5UV0	1.5 kW
784-0739	6SL3210-5BB22-2UV0	2.2 kW
784-0748	6SL3210-5BB23-0UV0	3 kW

#### Inverter Drives with Filter - 1-Phase - 200-240V

Stock-No.	Siemens MPN	Power Rate
883-8755	6SL3210-5BB11-2AV0	0.12 kW
883-8759	6SL3210-5BB12-5AV0	0.25 kW
883-8768	6SL3210-5BB13-7AV0	0.37 kW
883-8816	6SL3210-5BB15-5AV0	0.55 kW
883-8825	6SL3210-5BB17-5AV0	0.75 kW
883-8828	6SL3210-5BB21-1AV0	1,1 kW
883-8822	6SL3210-5BB21-5AV0	1,5 kW
883-8831	6SL3210-5BB22-2AV0	2,2 kW
883-8834	6SL3210-5BB23-0AV0	3 kW

#### Accessories

Stock-No.	Siemens MPN	Description
784-0836	6SL3255-0VE00-0UA0	Parameter Loader
784-0701	6SL3200-0UF03-0AA0	Replacement Fan

#### Inverter Drives without Filter - 3-Phase - 380-480V

Stock-No.	Siemens MPN	Power Rate
784-0745	6SL3210-5BE13-7UV0	0.37 kW
784-0757	6SL3210-5BE15-5UV0	0.55 kW
784-0760	6SL3210-5BE17-5UV0	0.75 kW
784-0767	6SL3210-5BE21-1UV0	1.1 kW
784-0779	6SL3210-5BE21-5UV0	1.5 kW
784-0782	6SL3210-5BE22-2UV0	2.2 kW
784-0789	6SL3210-5BE23-0UV0	3 kW
784-0791	6SL3210-5BE24-0UV0	4 kW
784-0805	6SL3210-5BE25-5UV0	5.5 kW
784-0802	6SL3210-5BE27-5UV0	7.5 kW
784-0814	6SL3210-5BE31-1UV0	11 kW
784-0827	6SL3210-5BE31-5UV0	15 kW

#### Inverter Drives with Filter - 3-Phase - 380-480V

Stock-No.	Siemens MPN	Power Rate
784-0741	6SL3210-5BE13-7CV0	0.37 kW
784-0754	6SL3210-5BE15-5CV0	0.55 kW
784-0751	6SL3210-5BE17-5CV0	0.75 kW
784-0763	6SL3210-5BE21-1CV0	1.1 kW
784-0776	6SL3210-5BE21-5CV0	1.5 kW
784-0773	6SL3210-5BE22-2CV0	2.2 kW
784-0785	6SL3210-5BE23-0CV0	3 kW
784-0798	6SL3210-5BE24-0CV0	4 kW
784-0795	6SL3210-5BE25-5CV0	5.5 kW
784-0808	6SL3210-5BE27-5CV0	7.5 kW
784-0811	6SL3210-5BE31-1CV0	11 kW
784-0818	6SL3210-5BE31-5CV0	15 kW



For more technical information please visit:  
[www.rs-online.com](http://www.rs-online.com)