



ENGLISH

Datasheet

RS Pro Tap Wrenches: T-Bar Type Ratchet Type

RS Stock No: 444-920



Specifications:

Ratchet Type

T-handles slide both ways for tightening

Hardened & tempered split collet chucks for positive grip

Knurled & hardened clamping nut

Spring tension holds handle in desired position

Handle: 142mm

Height: 120mm

A/F Range: 5-7mm

Order Code	Manufacturers Code	Description
444-920	4300-235	Tap Wrenches: T-Bar Type



ENGLISH

Datasheet

RS Pro Tap Wrenches: T-Bar Type Ratchet Type

Tap Range:

Square	ISO 529	ISO 529	DIN 352	ISO 529	ISO 529	ISO 529	ISO 529	ISO 529	ANSI
Dimensions	Metric Coarse	Metric Coarse	Metric Coarse	BSW	BSF	UNC	UNF	BA	NPT
	Full Diameter	Relieved Shank							
	Shank with Recess								
Size mm	Size	Size	Size	Size	Size	Size	Size	Size	Size
5	M6	M8	M6	1/4	1/4	1/4	1/4		
5.6	M7	M9							
5.9									1/16
6			M7						
6.3	M8	M10, M11		5/16, 7/16	5/16, 7/16	5/16, 7/16	5/16, 7/16		
6.8			M8						
7.1	M9	M12		1/2	1/2	1/2	1/2		