

Technical data sheet

Article number:
111-00642

T18R



Product Group	Cable ties polyamide 6.6 standard
Product Family	T-Series in PA66 natural
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)
Application Range	Indoor Use
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7ISP
Bundle Ø max.	22.0 mm
Bundle Ø min.	1.0 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	3.7 mm
Length (L)	100.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C
Package Content	1000 pcs.
Package Content packed in	bag
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 1565, ANSI/UL 62275
Thickness (T)	1.1 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E64962
UV-Stabilised	No
Variant	Inside Serrated
Width (W)	2.5 mm

