

Main

Range of product	Acti9
Product or component type	Remote indication auxiliary
Device short name	iSR
Signal contacts composition	1 C/O
[In] rated current	AC-12 3 A at 380...415 V, AC 50/60 Hz AC-12 6 A at 220...240 V, AC 50/60 Hz DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC
9 mm pitches	1





Complementary

Mounting mode	Fixed
Mounting support	DIN rail
Height	84 mm
Width	9 mm
Depth	69 mm
Colour	White
Connections - terminals	Clamp terminal (bottom) 3 cable(s) 0.16 mm ² - rigid Clamp terminal (bottom) 6 cable(s) 0.16 mm ² - flexible Clamp terminal (bottom) 1 cable(s) 0.16 mm ² - flexible with ferrule
Wire stripping length	9 mm
Tightening torque	1 N.M 1.2 N.m

Environment

Standards	EN/IEC 60947-5-1
IP degree of protection	IP20 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins