

Features

- Shock-Absorbing Tips: Polyurethane tips for controlled, non-marring strikes.
- Robust Build: Forged steel body ensures durability and long service life.
- Protective Collar: Nylon collar reduces wear and safeguards the mallet.
- Comfortable Grip: Varnished ash wood handle for ergonomic handling.
- Ideal for Delicate Work: Perfect for assembly, maintenance, and tasks requiring gentle impact.

RS PRO Polyurethane Mallet with Forged Steel Body, Nylon Collar & Varnished Ash Handle, 40mm Head Diameter

RS Stock No.: 0747540



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Polyurethane Mallet is engineered for precision and protection in industrial and workshop environments. Its polyurethane tips deliver non-marring strikes, making it ideal for delicate surfaces. The forged steel body provides strength, while the nylon collar adds extra durability. A varnished ash wood handle ensures comfort during prolonged use. This mallet is perfect for assembly, maintenance, and repair tasks where controlled force is essential.

General Specifications

Product Type	Polyurethane Mallet
Handle Material	Polyurethane
Body Material	Forged Steel
Collar Material	Nylon
Handle Material	Varnished Ash Wood
Head Diameter	40 mm
Overall Length	320 mm
Head Length	107 mm
Weight	528g