



AS PIC-234568 TL10

E1441376

Assortment Box Splicing Connectors 90pcs, Push-In



Product Properties:

Type of locking/unlocking	Push
Nominal voltage	450 V
Nominal current	24 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	2-8 .
With operation lever	No
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Colour	Multi-coloured

Dimensions:

Max. AWG-size	Other
Min. AWG-size	Other
Nominal cross section (device side)	0.5-2.5 mm ²
Nominal cross section (installation side)	0.5-2.5 mm ²
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-1.5 mm ²
Conductor cross section solid (solid, stranded)	0.5-2.5 mm ²
Width	190 mm

Height	40 mm
MOQ	1 .
Unit	pcs
Nominal cross section	0.5-2.5 mm ²
Length	150 mm
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
--------------------------	-----

Compliance:

REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Splicing Connectors - Assortment Boxes
Search Description	ENR2026V, EFO2026V
Alternative SKU	ASPIC-234568TL10
E-no	E1441376

Logistic information:

Barcode	733117643016
Country of origin	CN
E-no	E1441376
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	1 .
Stock code	AS PIC-234568 TL10
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.