

# Rhino™ M1011



## Industrial-Strength Metal Embossing Tool

- Uses 12 mm stainless steel and aluminum labels
- Built-in hole punch for creating hanging, screw-on or nail-on labels
- Built-in cable tie slot punch for cable marking
- Built-in measuring gauge – accurately set length of leading and trailing label edge
- Easy-to-use cutting handle makes cutting stainless steel labels effortless – cuts square or rounded edges
- Print mirror script labels with included reverse image character wheel
- Deep emboss ensures excellent character legibility
- Rugged cast aluminum frame withstands tough working conditions



### Single Unit Includes:

- M1011 Label Embosser
- Horizontal Character Wheel
- Reverse Image Character Wheel
- Roll 12mm x 4.80m Non-Adhesive Aluminum Labels
- Roll 12mm x 6.40m Non-Adhesive Stainless Steel Labels
- Hard Carry Case



Quick Specs	
Unit Dimensions (H x W x L)	214.88mm x 103.12mm x 56.89
Weight (excluding battery)	3.0 kg
Mac®/PC Compatible	No
Accepts Label Sizes	25.4mm
Tape Platform	IND Embossing
Resolution	N/A
Printing System	Manual
Print Speed	N/A
Barcodes	N/A
Cutter Type	Manual
Batteries	N/A
AC Adapter	N/A
Networking	No
Country of Origin	China

Item Number	Description		Length (cm)	Width (cm)	Height (cm)	Weight (kg)	QTY	UPC	Customer Price	
S0720090	RHINO M1011	Unit	11.3	3.8	4.4	3.0	1	5411313011105		
		Shelf	-	-	-	-	-	-	-	
		Case	15.5	13.5	7.0	9.1	3	15411313011102		
		Pallet	48.0	40.0	47.5	490.7	162	-		

## IND Embossing Labels

For heavy-duty and extreme condition labeling.

- Aluminum and stainless steel labels have excellent resistance to chemicals, extreme weather conditions, high and low temperatures and abrasion
- Ideal for marking pipelines, underground cables, engine parts, building materials and much more

Compatible Labels		
Width	Length	A
IND Non-Adhesive Aluminum Embossing Labels		
12 mm	384 m	31000
IND Non-Adhesive Stainless Steel Embossing Labels		
12 mm	504 m	32500
IND Adhesive Aluminum Embossing Labels		
12 mm	288 m	35800

Country of origin: China

**DISTRIBUTED BY:**  
DYMO, ATLANTA, GA 30328  
800-426-7827: WWW.DYMO.COM

13-0103



INTERNAL USE ONLY. NOT FOR DISTRIBUTION.

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.



A **NewellRubbermaid** Brand

©2013 SANFORD, L.P.

A NewellRubbermaid Company™	 <small>           1142 Mirinda Business Park            Chennai - 600 096 India            No. 143, Dr.M.G. Road            Sandhome Road Chennai 600 096 India            T: 91 44 4253 7777   www.schawk.com         </small>	 CYAN    MAGENTA    YELLOW    BLACK	
	Use the PANTONE MATCHING SYSTEM for accurate color reproduction		
	<b>VERSION</b>	<b>JOB DESCRIPTION:</b> NRM_EU_Writing_Dymo_1362812_EMEA Product Handbooks_UK Masters <b>FILE NAME</b> : DY_1362812_2014_EMEA_M1011_TechSheet_v4.indd	<b>BRAND</b> : WRITING-DYMO
<b>4</b> DATE : 10-15-2014 OPERATOR : SR	<b>SCHAWK JOB #</b> : 310253X <b>NRM JOB #</b> : 1362812 <b>COMPONENT #</b> : N/A	<b>CATEGORY OF WORK:</b> COLLATERALS-FACT BOOKS <b>NO. OF PAGES#</b> : 2 PAGE <b>SIZE</b> : A4	
NOTE :			