

## ROHS COMPLIANT

UNITS = INCHES [MM]

## NDTE:

MATERIAL HOUSING: CONTACT:

PBT UL94V-0, BLACK BRASS BRASS

NUT: D-RING:

EPDM, BLACK

FINISH CONTACT:

GOLD PLATED OVER 504 NICKEL NICKEL PLATED

NUT:

ELECTRICAL RATED CURRENT:

4A 60V

RATED VOLTAGE:
INSULATION RESISTANCE:

100 M□hms MIN. 10 m□hms MAX.

CONTACT RESISTANCE: WATER PROOF:

IP67

ENVIRONMENT

OPERATION TEMPERATURE:

-40°C T□ +85°C


MAX WIRE AWG:

22

## 858-005-103RLUY

3 = BRASS/NICKEL NUT — S = STAINLESS STEEL NUT

1 = GOLD FLASH - 4 = 10u'' GOLD



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON
DATE:
03-07-16

NorComp

SCALE:	SHEET OF	REV
NTS	1 1	3
DWG NO.	858-005-103RLUY	