

6500 - Model 813

Multi-layer chemical barrier technology for Type 1 / Limited Use Level A Gastight protection - Integral Sock, Passthrough & CEJN Connector

Multi-layer, gastight protective suit, granting wearers heightened chemical resistance..

- **Advanced protection:** The AlphaTec® 6500 Stitched & Taped - Model 813, with its lightweight, innovative twin-layer fabric, inner barrier glove and outer butyl rubber glove grants wearers superb chemical resistance
- **Improved visibility:** Due to its bright yellow exterior, this full-body protective suit is highly visible, thereby enhancing worker and workplace safety
- **Increased comfort and ergonomics:** Its large SCBA hump results in more ergonomic movements, which improves wearer comfort
- **Enhanced features:** This protective suit also boasts an integral sock, a passthrough and a CEJN connector



Industries

- Fire and Rescue
- Chemical
- Life Sciences
- Mining
- Oil and gas

Applications


- Contaminated Environments
- Chemical Handling
- Raw material sample collection
- Hazmat response
- Emergency Response
- Military

KEY FEATURES & BENEFITS


- **Lightweight twin-layer barrier:** Excellent chemical resistance*
- **Yellow color:** Enhanced visibility, for improved workplace safety
- **Enhanced features:** Large SCBA hump, integral sock, passthrough and CEJN connector
- **Protection against Chemical warfare agents:** Breakthrough time > 48 Hours for Seven warfare agents

**Type 1/Level A protection

Material Diagram



Seam Diagram



Performance Standards



Product Information

Product Information	
Available Sizes	S, M, L, XL, 2XL, 3XL
Color	Yellow
Country Of Origin	China
Models Available	803, 809, 813, 819
Packaging Overview	Individually packaged
Product Material	Twin multi layer barrier films laminated either side of non-woven fabric
Product Reference	6500 - Model 813
Standards Overview	• EN 943-1 • EN 14126 (infective agents) • Tested and compliant to EN 943-2 with the exception of the low temperature practical performance requirement
Seam Type	Stitched and Taped
Shelf Life	10 Years
Style Number	Y65A813M

Suit components & accessories

Suit Components and Accessories	
Design Features	Fully encapsulating Type 1 Limited Use Gastight Suit with integral socks, complete with straight outer leg. Side entry DYNAT G2 CR/PA gastight zipper, protected by a splash guard/flap. Other suit features include large SCBA hump, single sleeve, external locking cuff and GA2 glove set (AlphaTec® 02-100 barrier inner + AlphaTec® 38-560 butyl outer). Large hump for internal wearing of self-contained breathing apparatus. Passthrough device with CEJN 342 connector and plug. Rear positioned exhaust valves.
Visor And Face Seal	Large field of view GAG visor
Gloves And Attachments	AlphaTec® 02-100 & AlphaTec® 38-560
Footwear And Attachments	Sock Only
Zipper	DYNAT G2 CR/PA gastight zipper

For additional in formation visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Australia
Ansell Limited
T: +61 1800 337 041

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

