

Features

- Heavy duty steel construction
- Adjustable spill retaining shelves
- Non removable sump
- Warning labels
- Conforms to COSHH guidelines

RS PRO Yellow Lockable 2 Door Hazardous Substance Cabinet, 1800 x 1200 x 460mm

RS Stock No.: 0440936



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Hazardous Substance Cabinets

Our RS PRO hazardous substance cabinet is designed to provide safe storage for potentially dangerous substances and materials. Featuring steel construction, 2 Keys are provided with a chrome plated die-cast zinc handle (non snag) and a 2 point steel locking mechanism. A non-removable spillage sump is an integral part of the base to contain spillage. 3 adjustable shelves are provided which can retain minor spills and has a galvanised finish.

General Specifications

Height	1800mm
Width	1200mm
Depth	460mm
Lockable	Yes
Number of Doors	2
Number of Shelves	3
Colour	Yellow

Approvals

Declarations	REACH DoC
Standards Met	COSHH

Similar Products

Stock No.	Brand	Product Name	Dimension	No. of Door	Colour
0440936	RS PRO	Hazardous Cupboard 1800x1200x460mm	1800x1200x460mm	2	Yellow
0440911	RS PRO	Hazardous Cupboard 1800x900x460mm	1800x900x460mm	2	Yellow
0440913	RS PRO	Hazardous Cupboard 1200x900x460mm	1200x900x460mm	2	Yellow
0440914	RS PRO	Hazardous Cupboard 900x900x460mm	900x900x460mm	2	Yellow
0440915	RS PRO	Hazardous Cupboard 900x460x460mm	900x460x460mm	1	Yellow
0440917	RS PRO	Hazardous Cupboard 700x900x460mm	700x900x460mm	2	Yellow
0440918	RS PRO	Hazardous Cupboard 700x350x300mm	700x350x300mm	1	Yellow
0440920	RS PRO	Mobile Hazardous Cupboard 1040x900x460mm	1040x900x460mm	2	Yellow
0440921	RS PRO	Mobile Hazardous Cupboard 840x900x460mm	840x900x460mm	2	Yellow
0440923	RS PRO	Flo.Chest Hazar. Cupboard 610x1170x460mm	610x1170x460mm	N/A	Yellow
0440924	RS PRO	Wall Moun. Hazar. Cupboard 570x850x255mm	570x850x255mm	2	Yellow
0440926	RS PRO	Galvanised Extra Shelves 1200x460mm	1200x460mm	N/A	Yellow
0440927	RS PRO	Galvanised Extra Shelves 900x460mm	900x460mm	N/A	Yellow
0440929	RS PRO	Galvanised Extra Shelves 460x460mm	460x460mm	N/A	Yellow
0440930	RS PRO	Galvanised Extra Shelves 350x300mm	350x300mm	N/A	Yellow
0440932	RS PRO	Stand to suit 900x460mm	900x460mm	N/A	Yellow
0440933	RS PRO	Stand to suit 460x460mm	460x460mm	N/A	Yellow
0440935	RS PRO	Stand to suit 350x300mm	350x300mm	N/A	Yellow