

HT3-1000



The HandTorque[®] HT3-1000 has been designed for use where it is necessary to provide higher torques than would otherwise be possible due to limitations of space or operator strength. Input to the multiplier is via a ratchet torque wrench set to one fifth of the desired output torque. **Part number:** 180260

EAN Bar Code: 5060207565622

NATO number: -

Accuracy: $\pm 4\%$

Operates between:

100.0 - 1000.0 N·m

74.0 - 738.0 lbf·ft



TECHNICAL SPECIFICATIONS

- Tool Weight: 2.7 Kg
- Output Square: 3/4"
- Input Square: 1/2"
- Reaction Plate Weight: 0.5 Kg cranked / 0.69 Kg straight
- 5:1 nominal torque multiplication reaction dependant. Ratio with cranked foot is 4.8:1; with straight reaction being 4.9:1

FEATURES

- Quick change cranked reaction with improved flexibility allowing reaction in 8 orientations
- Robust construction means minimal maintenance and long life
- Small and compact design
- Supplied with 2 reaction bar styles for maximum versatility