

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


F

REV / 0L20-0042-96

07JAN97

ME

TM



1 STAMP AMP 12-10*APPROX AS SHOWN

2. WIRE INSUL DIA, 3.81-5.84 [.150-.230]

3. TONGUE MATL THK, 1.02 ± 0.05 [.040 ± .002]

500


LOOSE PIECE

323067

QTY

PACKAGE TYPE

PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMMAX RECOMMENDED OPERATING
TEMPERATURE:
343°C [650°F]THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
mm [in]TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-MATERIAL
BODY, CU PER ASTM B152
SLEEVE, NI SIL PER
ASTM B122FINISH
BODY, NP, QQ-N-290

DWN L OLMEDA 100CT94

CHK M ELLIS 100CT94

APVD S BORTNER 100CT94

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

AMP

AMP Incorporated
Harrisburg, PA 17105-3608NAME TERMINAL, RING TONGUE,
STRATO-THERM™, DIAMOND GRIP™,
WIRE SIZE, 12-10 AWG

SIZE

CAGE CODE

DRAWING NO

A3

00779

C-323067

SCALE 4:1

SHEET 1 OF 1

REV F