

LOGO! 9 TDE touch display, 256 colors, 2 Ethernet ports, for LOGO! 9

General information	
Product type designation	touch display
Suitability for use	can be used with LOGO! 9 and higher
Display	
Design of display	touch display
Resolution (pixels)	
<ul style="list-style-type: none"> <li>Horizontal image resolution</li> <li>Vertical image resolution</li> </ul>	480 pixel 272 pixel
Control elements	
Keyboard fonts	
<ul style="list-style-type: none"> <li>System keys</li> <li>alphanumeric keyboard</li> </ul>	Yes No
Installation type/mounting	
Wall mounting/direct mounting	No
Supply voltage	
Type of supply voltage	AC/DC
Rated value (DC)	12 V; 12/24 V DC, 24 V AC
Power loss	
Power loss, typ.	1.92 W; At 24 V DC
Interrupts/diagnostics/status information	
Diagnostics function	No
Degree and class of protection	
IP (at the front)	IP65
IP (rear)	IP20
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
FM approval	Yes
KC approval	Yes
Ecological footprint	
<ul style="list-style-type: none"> <li>environmental product declaration</li> </ul>	Yes
Global warming potential	
<ul style="list-style-type: none"> <li>— global warming potential, (total) [CO2 eq]</li> <li>— global warming potential, (during production) [CO2 eq]</li> <li>— global warming potential, (during operation) [CO2 eq]</li> <li>— global warming potential, (after end of life cycle) [CO2 eq]</li> </ul>	44.33 kg 9.4 kg 35.08 kg -0.15 kg
Marine approval	
<ul style="list-style-type: none"> <li>American Bureau of Shipping (ABS)</li> </ul>	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> <li>min.</li> <li>max.</li> </ul>	-20 °C; No condensation 55 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> <li>min.</li> <li>max.</li> </ul>	-40 °C 70 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> <li>Ambient air temperature-barometric pressure-altitude</li> </ul>	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)

Configuration	
Configuration software	
• Configuration tool	LOGO! Soft Comfort V9 or higher
Accessories	
belongs to product	LOGO! 9
Mechanics/material	
Design of housing	plastic
Dimensions	
Width	128.2 mm
Height	86 mm
Depth	38.7 mm
Mounting cutout, width	119 mm; Tolerance +0.5 mm
Mounting cutout, height	78.5 mm; Tolerance +0.5 mm
Weights	
Weight, approx.	205 g
Approvals / Certificates	
General Product Approval	



[Manufacturer Declaration](#)

[China RoHS](#)



General Product Approval

For use in hazardous locations

Environment



[CCC-Ex](#)



last modified:

5/9/2026