

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Sensor/actuator cable, 5-pos., free cable end to straight M12 socket, A-coded, cable length: 5 m



Commercial data

Item number	1405342
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	AF1CDA
GTIN	4046356740630
Weight per piece (including packing)	428.9 g
Weight per piece (excluding packing)	415 g
Customs tariff number	85444290
Country of origin	PL

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	No

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

Cable/line

Cable length	5 m
--------------	-----

POC irradiated halogen-free black [BF 145]

Cable weight	86 kg/km
Number of positions	5
Shielded	yes
Cable type	POC irradiated halogen-free black [BF 145]
AWG signal line	20
Conductor cross section	5x 0.5 mm ²

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Wire diameter incl. insulation	1.9 mm
External cable diameter	7.30 mm
Outer sheath, material	POC
External sheath, color	black RAL 9005
Conductor material	Tin-plated Cu litz wires
Material wire insulation	POC
Single wire, color	black 1, black 2, black 3, black 4, black 5
Overall twist	5 wires around filler to the core
Nominal voltage, cable	300 V
Test voltage Core/Core	3500 V
Test voltage Core/Shield	2500.00 V
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	12 x D
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	88 mm
Dynamic load capacity (bending)	Max. bending cycles: 2000000, Bending radius: 10 x D, Traversing path: 5 m, Traversing rate: 4 m/s, Acceleration: 5 m/s²
Halogen-free	according to IEC 60754-1
	in accordance with DIN EN 50267-2-1
Flame resistance	IEC 60332-1
	According to DIN EN 50265-2-1
Concentration of fumes	in accordance with IEC 61034
	EN 50268-2
Other resistance	Good resistance to aggressive media
Special properties	Irradiated
Ambient temperature (operation)	-55 °C ... 145 °C (cable, fixed installation)
	-35 °C ... 120 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable

1405342

<https://www.phoenixcontact.com/in/products/1405342>


Drawings

Dimensional drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Circuit diagram



Contact assignment of the M12 socket

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P- 5,0-BF145/M12FS SH NC - Sensor/actuator cable



1405342

<https://www.phoenixcontact.com/in/products/1405342>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in