



ANCIENS

NOUVEAUX

Climatiseurs pour montage latéral				Climatiseurs pour montage latéral			
Puissance frigorifique en régime permanent W	Tension V	Référence		Référence	Tension V	Régulation	Puissance frigorifique en régime permanent W
350	230	3203.100		3302.100	230	Basic	300
	115	3205.100		3302.110	115		
680	230	3269.100		3303.100	230	Basic	500
	115	3262.100		3303.110	115		
				3303.500	230		
			3303.510	115	Confort		
825/1100	230	3293.100 /	3393.100	3304.100	230	Basic	1000
	115	3281.100 /	3381.100	3304.110	115		
	400	3293.140 /	3393.140	3304.140	400/460		
	230	3293.500 /	3393.500	3304.500	230		
	115	3281.500 /	3381.500	3304.510	115		
	400	3293.540 /	3393.540	3304.540	400/460		
1400	230	3298.100		3305.100	230	Basic	1500
	115	3279.100		3305.110	115		
1760	400	3260.140		3305.140	400/460		
1400	230	3298.500		3305.500	230	Confort	2000
	115	3279.500		3305.510	115		
1760	400	3260.500		3305.540	400/460		
2000	230	3390.100		3328.100	230	Basic	2500
	115	3390.115		3328.110	115		
	400	3390.140		3328.140	400/460		
	230	3390.500		3328.500	230		
	115	3390.515		3328.510	115		
	400	3390.540		3328.540	400/460	Confort	
2500	230	3392.100		3329.100	230	Basic	4000
	115	3392.115		3329.110	115		
2600	400	3394.140		3329.140	400/460		
2500	400	3392.140		3329.500	230	Confort	2500
	230	3392.500		3329.510	115		
	115	3392.515		3329.540	400/460		
2600	400	3394.500					
2500	400	3392.540					
4000	400	3391.140		3332.140	400/460	Basic	4000
	400	3391.500		3332.540		Confort	