




Process adapters pipe fitting DIN11851

ADAPT DIN11851 DN50



Application		
Design	for volumetric flow meters SMF	
Application	food and beverage industry; hygienic systems	
Pressure rating	25 bar	2.5 MPa
Tests / approvals		
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	
Mechanical data		
Weight	[g]	2882
Materials	stainless steel (316L/1.4404)	
Nominal diameter	DN50 (2")	
Sensor connection	ifm-specific device flange	
Process connection	hygienic pipe fitting DIN 11851	
Process connection suitable for pipe standard	(DIN EN 10357 series A); (DIN 11866 series A); (DIN 11850 series 1); (DIN 11850 series 2)	
Surface characteristics Ra/Rz of the wetted parts	Ra ≤ 0.4 µm	

E40503



Process adapters pipe fitting DIN11851

ADAPT DIN11851 DN50

Accessories	
Items supplied	screws 8
Remarks	
Pack quantity	2 pcs.