

Drywall Cutter LXT®

DCO180

18V • 30 000 min⁻¹

Quick and handy drywall cutter

A light cutter for cutting holes and shapes in drywall.
Speed of 30 000 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
No load speed	30000 min ⁻¹
Collet Capacity	3,18 / 6,35 mm
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	313 x 77 x 118 mm
Sound Power Level (L _{WA})	88 dB(A)
Product net weight	1,2 kg
Vibration Level, Rotation Without Load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Rotation Without Load	1,5 m/s ²
Vacuum cleaner connection Ø in / out	25 / 31 mm

User benefits

- Slim body design for a good grip
- Electronic overload protection protects the user and the device
- Anti-restart function minimises accidental start-up
- Battery protection system automatically shuts off power when the battery level is low
- Lock-on feature for continuous operation

Link to product - www.makita.dk



Related products

■ Optional AC

763677-9

Collet Cone 1/8"



■ Other

User manual

Parts drawing