


# ENGLISH

## RS Pro M12 Panel Mount Male 5W 100mm, PG9


RS Stock No: 144-7605





All dimensions are in mm.

#### **Pin Assignment**



### General Specification Rated Operational Voltage

Current Rating	4A
Insulation Resistance	>= 100 MΩ
Temperature Range	-25°C +75°C
Degree of Protection	IP67

60 V

#### **Material Specification**

Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
O-Ring	Neoprene
Pole	5
Clamp Nut	PG9

#### **Cable Specification**

Cross Section of Wire Termination Cable length 0.34 sq.mm Partially Stripped 100 mm