



15/32-32 THD

Specifications:

Operating temperature: -50°C to +150°C
 Mechanical life: min. 200 000 cycles
 Storage life: over 25 years
 Resistance: salt spray; sunlight; ozone; weather;
 fungus and most acids and lubricating oils
 Material: Rubber: silicone rubber TSE221
 Metal: brass
 Types: ET 207 - grey
 ET 209 - red



| | | | | |
|---|--|-------|-----------------------|-------------------|
| Tolerances: 0.00: ±0.05mm 0.0: ±0.10mm | | Date | Name | <h1>ET 20x</h1> |
| | | 08/08 | dr | |
| | | | | |
| | | | | |
| | | | | |
| | | | knitter-switch | <h1>30 15 57</h1> |
| Modifications | | Date | Name | Page 1/1 |