

Inspection Premium Handlamps



Description

This range of Elwis Inspection Premium Handlamps are extremely robust. They can be used indoors and outdoors at low temperatures, are resistant to oil and petrol, and do not present a fire hazard.

Features

- Robust construction with ABS body
- Available in 230V, 110V and 24V versions
- Pre fitted 13A plug on 230V versions
- Non-flicker light does not tire eyes
- Incorporate a flexible hanging hook
- Supplied with 5m flex
- 1 year guarantee

Range

8W T5 handlamp 110V	19E110
8W T5 handlamp 230V	19E008
11W PL handlamp 24V	19E1024
11W PL handlamp 110V	19E1100
11W PL handlamp 230V	19E1000

Technical Specification

	24V ac/dc
Voltage	110V ~ 50Hz
	230V ~ 50Hz
Lamp	8W T5 tube
	11W 4pin PL
Lumen Output	400 lumen (T5)
	900 lumen (PL)
IP Rating	IP65

Length (inc. hook)

19E110	510mm
19E008	510mm
19E1024	455mm
19E1100	455mm
19E1000	455mm
19E008	455mm

Standards

- BS EN 60598-2-8
- BS 4533
- BS 1363