

Pan-Wrap™ Installation Tools

- Patented installation tool with 180° opening allows easy loading of maximum bundle diameters to speed installation, providing the lowest installed cost




Part Number	Color	For Use With	Std. Pkg. Qty.*
PWT38	White	PW38F- Series	1
PWT50	White	PW50F- Series	1
PWT75	White	PW75F- Series	1
PWT100	White	PW100F- Series	1
PWT150	White	PW150F- Series	1

*Order number of tools required.

Spiral Wrap

- Harness multiple cables into a single manageable bundle
- Allows breakouts of single/multiple cables
- Provides protection for cables
- Multiple colors allow easy identification of cable bundles
- Reusable
- General purpose material for use up to 122°F (50°C);
Flame retardant material for use up to 167°F (75°C)
- Installation tool supplied in each package
- Outside diameter: 0.50" (12.7mm)
- Wall Thickness: 0.06" (1.52mm)
- Bundle range: 0.38" – 4.00" (9.5mm – 101.6mm)
- Packaged on a 100' (30.5M) reel for easy handling and dispensing of product



Part Number	Material	Color	Length of Reel‡		Std. Pkg. Qty.*
			Ft.	m	
T50F-C	Polyethylene	Natural	100	30.5	1
T50F-C0	Weather Resistant Polyethylene	Black	100	30.5	1
T50F-C1	Polyethylene	Brown	100	30.5	1
T50F-C2	Polyethylene	Red	100	30.5	1
T50F-C3Y	Polyethylene	Orange	100	30.5	1
T50F-C4Y	Polyethylene	Yellow	100	30.5	1
T50F-C5	Polyethylene	Green	100	30.5	1
T50F-C6	Polyethylene	Blue	100	30.5	1
T50F-C7	Polyethylene	Purple	100	30.5	1
T50F-C8	Polyethylene	Gray	100	30.5	1
T50F-C10	Polyethylene	White	100	30.5	1
T50F-C16	Polyethylene	Pink	100	30.5	1
T50FR-CY**	Flame Retardant Polyethylene	White	100	30.5	1
T50FR-C20Y**	Flame Retardant Polyethylene	Black	100	30.5	1

‡Reel packaging may contain splices.

*Order number of reels required.

**Flame retardant products are manufactured from a material that is rated UL 94V-0 and RoHS compliant. Contact Panduit Customer Service for additional sizes and materials available.