

Abox GT 025

80 x 80 x 52 mm

IP 68

Description



Junction box - **Industrial Quality** - according to DIN EN 60529 and DIN VDE 0278-623, weather-proof and resistant, $U_i=690$ V, with soft sealing entry membranes M20, seal range 2 - 16 mm, with cast-resin bags 250 ml (no product code), funnel, ventilation plug and disposable gloves

Order No. Packing Qty



Entries

Abox GT 025 - 2.5²
grey, with screw terminals 5-poles - 2.5 mm²
(4 x 1.5² / 4 x 2.5²)

492 402 01

1/1

Abox GT 040

93 x 93 x 55 mm

IP 68



Junction box - **Industrial Quality** - according to DIN EN 60529 and DIN VDE 0278-623, weather-proof and resistant, $U_i=690$ V, with soft sealing entry membranes M20, seal range 2 - 16 mm, with cast-resin bags 250 ml (no product code), funnel, ventilation plug and disposable gloves



Entries

Abox GT 040 - 4²
grey, with screw terminals 5-poles - 4 mm²
(4 x 1.5² / 4 x 2.5² / 3 x 4²)

492 404 01

1/1

Abox GT 060

110 x 110 x 67 mm

IP 68



Junction box - **Industrial Quality** - according to DIN EN 60529 and DIN VDE 0278-623, weather-proof and resistant, with double membrane seals M25, seal range 9-16 mm, with cast-resin bags 600 ml (no product code), funnel, ventilation plug and disposable gloves



Entries

Abox GT 060 - 6²
grey, with screw terminals 5-poles - 6 mm²
(4 x 2.5² / 4 x 4² / 3 x 6²)

492 406 01

1/1


Abox GT 100

140 x 140 x 79 mm

IP 68



Junction box - **Industrial Quality** - according to DIN EN 60529 and DIN VDE 0278-623, weather-proof and resistant, with double membrane seals M32, seal range 14-21 mm, with cast-resin bags 1200 ml (no product code), funnel, ventilation plug and disposable gloves



Entries

Abox GT 100 - 10²
grey, with screw terminals 5-poles - 10 mm²
(4 x 4² / 4 x 6² / 3 x 10²)

492 410 01

1/1