

[Home](#) > [Products](#) > [Fuses](#) > [NH Blade Fuses](#) > [NH 1](#) >

NH1 General Line (gG/gL) 500VAC and 690VAC Blade Type Fuse

Siba General Line fuses. Also referred to as gL/gG. General purpose fuses. Sizes available from NH00/NHC000 to NH4. Din 43 620. VDE 0636/201 Breaking Capacity AC = 120KA. Voltage rating = 500VAC. Blade type fuse, with indication on the top and side for extra visibility.

Amperage rating for the NH1 size from 16A upto 250A. (500VAC) Fuse Bases available. Fuse puller / handle available. 690VAC NH00 (20-211-13) fuses available (80KA) NH Solid links available from size 00 (NH00) upto size 4 (NH4).



partnumber

20-003-13/100A
20-003-13/125A
20-003-13/160A
20-003-13/16A
20-003-13/200A
20-003-13/224A
20-003-13/250A
20-003-13/50A
20-003-13/63A
20-003-13/80A
20-211-13/100A
20-211-13/125A
20-211-13/160A
20-211-13/200A

description

NH1 100A GL DIN 500V BLADE
NH1 125A GL DIN 500V BLADE
NH1 160A GL DIN 500V BLADE
NH1 16A GL DIN 500V BLADE
NH1 200A GL DIN 500V BLADE
NH1 224A GL DIN 500V BLADE
NH1 250A GL DIN 500V BLADE
NH1 50A GL DIN 500V BLADE
NH1 63A GL DIN 500V BLADE
NH1 80A GL DIN 500V BLADE
NH1 100A GL DIN 690V BLADE
NH1 125A GL DIN 690V BLADE
NH1 160A GL DIN 690V BLADE
NH1 200A GL DIN 690V BLADE

[Home](#) | [Contact](#) | [Company](#) | [Distributors](#) | [News](#) | [Products](#) | [Sitemap](#)

Europa Components & Equipment Plc

Europa House, 108 Ripon Way,
Borehamwood, Herts,
WD6 2JA - UK

Tel: 0208 207 0440 Fax: 0208 207 6646

email: sales@europacomponents.com
europacomponents.com

© Copyright 2003 all rights reserved