


Loc J	DIST —	REVISIONS 変更			DATE	DWN	APVD
		P	LTR	DESCRIPTION			
			01	REVISED ECR-07-000882	12JAN2007	T.K	D.M



- 注)
 1.一般公差：±0.25
 2.材料：銅合金全面Niめっき1.3μm以上
 接点部金めっき0.38μm以上めっき
 3.適用電線：AWG#16-#14(被覆外径φ2.0~φ3.75)

- NOTES)
 1.GENERAL TOLERANCE:±0.25
 2.MATERIAL:COPPER ALLOY,FINISH:OVER NI PLATING 1.3μm MIN.
 (CONTACT AREA) 0.38μm MIN GOLD PLATING
 3.APPLICABLE WIRE:AWG#16-#14 (INS DIAφ2.0~φ3.75)

M SIZE

1747499-2
PART NUMBER

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. BY TYCO ELECTRONICS CORPORATION.

DIMENSIONS: 単位：特 MM TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - 	DWN T.KUDO 26AUG2004	MATERIAL 材料 COPPER ALLOY	FINISH 仕上 —
	CHK D.MITSUGI 26AUG2004	Tyco Electronics AMP K.K. Kawasaki,Japan	
	APVD D.MITSUGI 26AUG2004	NAME 名称 DYNAMIC D-4200 REC CONTACT M SIZE LOOSE PIECE	
	PRODUCT SPEC 製品規格 108-78182	SIZE A4	CAGE CODE 00779
APPLICATION SPEC 取付適用規格 114-5369	WEIGHT —		RESTRICTED TO —
CUSTOMER DRAWING			SCALE 尺度 4:1
			SHEET 1 OF 1
			REV 01