

Expressions Revive

Electric Shower

Best in its class, the superior Expressions Revive offers unrivalled flexibility and ease of installation, while its sleek, slim profile and contemporary chrome accessories blend beautifully with modern bathrooms.



Key features

- SmartFit2™ connectivity makes installation easy, thanks to multi-entry options
- Choice of 8 water pipe entry points (compression and push fit), 6 cable entry points and left or right hand electrical dual terminal block connections
- Large, removable lower backplate improves working space
- Multiple legacy wall fixings for easy replacement of existing showers
- Special push fit compression adaptor included as standard for universal installation
- Full chrome accessory FlexiFit™ kit included, complete with riser rail, hose and showerhead with six spray modes
- Easy to use, with start/stop push button and separate elevated dials for temperature and flow control
- Push button Start/stop with power on neon indication



Technical information

Performance: available in 7.2kW, 8.5kW and 9.5kW

Water: operating water pressure 1-10bar (15 – 150psi), with 15mm plain shank for push fit or standard 1/2" BSP compression fittings

Entry points: 2 top, 2 bottom, 2 rear and 2 side options for compression and push fit pipe connections and 2 top, 2 bottom and 2 rear options for cable entry



Technical information

Performance: available in 7.2kW, 8.5kW and 9.5kW

Water: operating water pressure 1-10bar (15 – 150psi), with 15mm plain shank for push fit or standard 1/2" BSP compression fittings

Entry points: 2 top, 2 bottom, 2 rear and 2 side options for compression and push fit pipe connections and 2 top, 2 bottom and 2 rear options for cable entry

Catalogue Number	Model/Description	Energy Rating	Efficiency (%)	kWh/Year Q elec	Noise (dB)	Load Profile
53563002	X7R Expressions Revive 7.2kW	A	38.62	478	15	XS
53563202	X8R Expressions Revive 8.5kW	A	38.56	478	15	XS
53563402	X9R Expressions Revive 9.5kW	A	38.47	477	15	XS



SMARTFIT2

