

## ESU137 electro-hydraulic tool kit

Ref.

### ESU137K1BLCM

See accessories for adapters required for the dies used.

Kit composition	Ref.
Crimping tool	<b>ESU137</b>
2 batteries 18 V / 5 Ah	<b>BL1850B</b>
Charger 220 V	<b>CLM1890HC</b>
Metallic carry case	<b>CMES120KN</b>



## Additional equipment for ESU137:

### Metallic carry case

- Ideal for transport and storage.
- Adapted to each model.

Ref.

### CMES120KN

### Fast charger

- Charger with display which identifies the state of the battery and the conditions of load.
- Charging time: 36 min.
- Weight: 0.85 Kg.
- Voltage: 220-240 V AC.
- Plug: Standard EU, others on request.



Ref.

### CLM1890HC

### Battery

- Li-Ion technology without memory effect.
- Voltage: 18 V.
- Capacity: 5.0 Ah.
- Weight: 0.64 Kg.



Ref.

### BL1850B

### BE2 support

- Support for fixing our BE2 crimping tools to a workbench.
- Compatible with our references: ESD50, ESDC60, ESDC80, ESU137.



Ref.

### SUPPORT OUTIL BE2

## Crimping dies:

Dies	Cross section (mm <sup>2</sup> )	Terminals series	Ref.	
			Dies	Adapters
 	10	pre-insulated ELP series	<b>ELP460</b>	U137-460
	16	pre-insulated FLP series	<b>FLP460</b>	U137-460
	25	pre-insulated NP series	<b>NP460</b>	U137-460
	10	non insulated ELS series	<b>ELS460 ou C12 ELS</b>	U137-460 or U137C12
	16	non insulated FLS series	<b>FLS460 ou C12 FLS</b>	U137-460 or U137C12
	25	non insulated TN 25 series	<b>C12TN25</b>	U137C12
	35	non insulated TN35 series	<b>C12TN35</b>	U137C12
	50	non insulated TN 50 series	<b>C12TN50</b>	U137C12
	70	non insulated TN70 series	<b>C12TN70</b>	U137C12
	95	non insulated TN95 series	<b>C12TN95</b>	U137C12
	120	non insulated TN120 series	<b>C12TN120</b>	U137C12
	150	non insulated TN150 series	<b>C12TN150</b>	U137C12
	185	non insulated TN185 series	<b>C12TN185</b>	U137C12
	240	non insulated TN240 series	<b>C12TN240</b>	U137C12