

Professionally approved products.


Datasheet

DC Axial Fan, 172 Dia. x 51mm, 391m³/h, 5W, 12 V dc (OD127SAP Series)

RS Stock 624-6577



Dimensions: (mm)



Professionally approved products. **Datasheet**

Specifications

• Impeller & Frame: Aluminium Die Cast, Black

Available Options

- Tachometer
- Locked Rotor Alarm
- Thermal Speed Control
- MOTOR: Brushless DC, polarity protected, locked rotor protected (current limited), auto restart
- INSULATION RESISTANCE Min. 10M ohms at 500VDCLIFE EXPECTANCY (L10): Ball Bearing 60,000 Hours
- Operating Temperature -10C ~ +70C
- Safety Approvals: UL/CUL, TUV, CE

RS Part No.
6196696
6246577
6196719

Speed	Airflow	Noise	Volts	Voltage	Current	Connection Type
3300	230	52	12	9~13	1.9	Wire
3300	230	52	12	9~13	1.9	Terminal
3300	230	52	24	12~27.6	1.0	Wire