

## Technical data sheet

Article number:  
151-04506

**FNTLOK01BK**

<b>Product Group</b>	Fast'N'Tube ®
<b>Material</b>	Polyamide 6.6, UV-stabilised (PA66UV)
<b>Colour</b>	Black (BK)
<b>Flammability</b>	UL 94 HB
<b>for Hole Ø (FH)</b>	8.0 mm
<b>Length (L)</b>	44.3 mm
<b>Length (L2)</b>	37.1 mm
<b>Operating Temperature</b>	-40 °C to +85 °C, (+105 °C, 500 h)
<b>Package Content packed in</b>	carton
<b>Pack Cont.</b>	100 pcs.
<b>Panel Thickness</b>	37.1 mm
<b>ROHS compliant</b>	Yes

HF ✓

RoHS ✓