

**ENGLISH** 


## **Datasheet**

## AC Axial Fan, 119.5 x 119.5 x 38.5mm, 187m/h, 12W, 115 V ac

RS Stock number 789-7892

Dimensions: (mm)





## **Specifications**

Frame	Diecast Aluminum	Notes	Г
Impeller	PBT, UL94V-0	Date: 041912	1
Connection	2x Lead Wires or terminals	Available Options Dual Voltage	
Motor	AC shaded pole, impedance and thermally protected		
Bearing System	Ball or Sleeve bearing		
Insulation Resistance	DC500V 100M ohm between lead wire and frame (500VDC)	* Specify configuration: TB = Terminal, Ball bearing WB = Wire leads, Ball bearing TS = Terminal, Sleeve bearing	
Dielectric Strength	1 minute at 1500VAC, max. leakage < 500 MicroAmp	WS = Wire leads, Sleeve bearing	
Temperature Range	-20C ~ +80C (ball) -10C ~ +50C (sleeve)		
Life Expectancy	40000 hours L10 (40C) 20000 hours L10 (40C)		

